

Mini Cup Switch



The Mini Cup switch features a 1-in/2.5-cm activation surface that provides auditory click and tactile feedback, and requires 4.2-oz/130-g of force to activate.

A smaller version of the Cup Switch for users with good targeting ability. Easily activated with finger or chin. Includes five colored stickers.

MINI CUP SWITCH TECHNICAL SPECIFICATIONS:

- Switch Type: Mechanical
- Connection Type: Wired
- Activation Type: Pressure
- Activation Surface: 1-in/2.5-cm diameter
- Activating Force: 4.2-oz/130-g
- Travel Before Activation: 0.01-in/0.03-cm
- Feedback: Auditory click, Tactile
- Plug Size: 1/8-in/3.5-mm mono
- Mounting Plate: Mini Cup & Trigger Plate